


DPU-2 data processing unit



Specification

System principal application	Hosts programming and data analysis software for use with Renishaw probing systems.
Part number	A-5465-4002
Compatible software applications	Productivity+™ CNC plug-in, SPRINT™ toolkits (see relevant application documentation for part numbers)
Physical	
Size	200 mm × 148.4 mm × 54.7 mm (7.87 in × 5.845 in × 2.15 in) (without DIN rail mounting and brackets)
Weight	1800 g (63.49 oz)
Mounting	DIN rail mount
Environmental	
IP rating	IP3X BS EN 60529:1992+A2:2013 (IEC 60529:1989+A1:1999+A2:2013)
Operating temperature	+5 °C to +55 °C (+41 °F to +131 °F) BS EN 60068-2-30:2005 (IEC 60068-2-30:2005)
Humidity	Maximum 93% RH at +40 °C
Cooling	Fanless
Connectivity	
USB	2 × USB 2.0: 2 × USB 3.0
Ethernet	3 × GbE LAN ports
Display	1 × HDMI: 1 × VGA
Power supply	
Voltage	24 V DC ±10% (powered from CNC machine tool)
Protection	Reverse voltage, over current, over voltage
Power consumption	17 W (typical)
Connector	2-pin Phoenix connector
Power on	Auto-on
Certification	CE, FCC
System storage	128 GB solid-state drive

Connections



Mounting the DPU-2



Dimensions given in mm (in)

For worldwide contact details, visit www.renishaw.com/contact

