


RESOLUTE™ absolute optical encoder with *BiSS* serial communications



RESOLUTE™ is a revolutionary true absolute, fine pitch optical encoder system, with excellent dirt immunity, offering an impressive specification that breaks new ground in position feedback.

Patented RESOLUTE technology combines 1 nm resolution with exceptionally high speed, up to 100 m/s (36 000 rev/min), reading from a range of high-accuracy linear tape and spar scales or angle encoder rings.

RESOLUTE uses a single optical absolute track with a nominal pitch of 30 µm, combined with sophisticated optics. This ensures wide set-up tolerances, very low sub-divisional error of ±40 nm and ultra-low noise (jitter) of less than 10 nm RMS, resulting in better velocity control performance and rock solid positional stability.

RESOLUTE ensures reliability with excellent dirt immunity, built-in separate position-checking algorithm and IP64 sealed readhead with wipe-clean recovery.

RESOLUTE is available with a variety of serial protocols. Contact your local Renishaw representative for details.

- True absolute non-contact optical encoder system: no batteries required
- Wide set-up tolerances for quick and easy installation
- High immunity to dirt, scratches and light oils
- Resolutions to 1 nm or 32 bit rotary
- 100 m/s maximum speed for all resolutions (to 36 000 rev/min)
- ±40 nm sub-divisional error for smooth velocity control
- Less than 10 nm RMS jitter for improved positional stability
- Built-in separate position-checking algorithm provides inherent safety
- IP64 sealed readhead for high reliability in harsh environments
- Integral set-up LED enables easy installation and provides diagnostics at a glance
- Readhead and linear/rotary scales are bolt-hole compatible with SIGNUM™ encoders
- Operates up to 80 °C
- Integral over-temperature alarm

Compatible with:



- RELA low-expansion, high-stability spar scales
- RSLA stainless steel spars
- RTLA with *FASTRACK*™ carrier
- RTLA-S self-adhesive tape scale
- RESA angle encoders
- Ultra-high accuracy REXA angle encoders

System features




Unique single-track absolute optical scale

- ▶ Absolute position is determined immediately upon switch-on
- ▶ No battery back-up
- ▶ No yaw de-phasing unlike multiple-track systems
- ▶ Fine pitch (30 µm nominal period) optical scale for superior motion control compared to inductive, magnetic or other non-contact optical absolute encoders
- ▶ High-accuracy graduations marked directly onto tough engineering materials for outstanding metrology and reliability



High dirt immunity

- ▶ Advanced optics and embedded surplus code mean RESOLUTE even reads dirty scale
- ▶ Absolute position can be determined in all three cases shown here; clean scale (left), grease contamination (below-left), particle contamination (below)



Unique detection method

- ▶ Readhead acts like an ultra-fast miniature digital camera, taking photos of a coded scale
- ▶ Photos are analysed by a high-speed digital signal processor (DSP) to determine absolute position
- ▶ Built-in position-check algorithm constantly monitors calculations for ultimate safety and reliability
- ▶ Advanced optics and position determination algorithms are designed to provide low noise (jitter < 10 nm RMS) and low sub-divisional error (SDE ±40 nm)

Range of rotary (angle) and linear scales

- ▶ Tough RELA low-expansion nickel alloy spars with ±1 µm accuracy up to 1 metre. Available in lengths up to 1.5 metres.
- ▶ Shatter-proof RSLA stainless steel scale, offering higher accuracy than glass scales and long lengths up to 5 metres, with ±4 µm accuracy over a complete 5 metre length
- ▶ RTLA with *FASTRACK*, and RTLA-S tape scales with ±5 µm/m accuracy and easy installation
- ▶ RESA ring with unique taper mount has large through hole for easy installation
- ▶ REXA ultra-high accuracy ring with ±1 arc second total installed accuracy with dual readheads

Range of protocols and resolutions

Protocol	Resolutions	
	Linear	Rotary
BiSS	50 nm	18 bit
	5 nm	26 bit
	1 nm	32 bit

Other serial protocols are available. Contact your local Renishaw representative for information.

Linear absolute encoder version

Resolutions and scale lengths

The maximum scale length is determined by the readhead resolution and the number of position bits in the serial word. For RESOLUTE readheads with fine resolution and short word length, the maximum scale length will be limited accordingly. Conversely, coarser resolutions or longer word lengths enable the use of longer scale lengths.

RESOLUTE is available with a variety of serial protocols. The example shows RESOLUTE using BiSS-C (uni-directional) protocol with three options for the position word length; 36 bit, 32 bit and 26 bit.

The 36 bit and 32 bit position words facilitate longer lengths that can be a significant benefit, especially at fine resolutions.

Resolution	1 nm	5 nm	50 nm
Maximum scale length (L) with 36 bit position word	21 m	21 m	21 m
Maximum scale length (L) with 32 bit position word	4.295 m	21 m	21 m
Maximum scale length (L) with 26 bit position word	67 mm	336 mm	3.355 m
Maximum reading speed	100 m/s	100 m/s	100 m/s

Contact your local Renishaw representative for details of other serial protocols.

Scale specifications

For more detailed scale information please refer to the relevant scale data sheet

Description	RELA	High-performance low-expansion spar scale for very high-accuracy applications. Lengths up to 1.5 m
	RSLA	High-performance stainless steel spar scale for very high-accuracy applications with longer axis lengths. Lengths up to 5 m
	RTLA/FASTRACK	Track-mounted hardened stainless steel tape scale for high-performance motion control systems requiring easier and faster scale installation and field replacement. RTLA lengths up to 21 m FASTRACK lengths up to 25 m
	RTLA-S	Self-adhesive hardened stainless steel tape scale for high-performance motion control systems requiring simple installation. Lengths up to 21 m
Accuracy (@ 20 °C)	RELA	±1 µm up to 1 m ±1 µm/m for lengths from 1 m to 1.5 m
	RSLA	±1.5 µm up to 1 m ±2.25 µm for lengths from 1 m to 2 m ±3 µm for lengths from 2 m to 3 m ±4 µm for lengths from 3 m to 5 m
	RTLA/FASTRACK	±5 µm/m
	RTLA-S	±5 µm/m
Coefficient of thermal expansion (@ 20 °C)	RELA	0.75 ±0.35 µm/m/°C
	RSLA	10.1 ±0.2 µm/m/°C
	RTLA/FASTRACK	10.1 ±0.2 µm/m/°C
	RTLA-S	10.1 ±0.2 µm/m/°C

Angle absolute encoder version

Resolution

RESOLUTE is available with a variety of resolutions, to meet the needs of a wide range of applications.

The choice of resolutions depends on the serial protocol being used, but there are no limitations due to ring size; for example *BiSS* 26 bit resolution is available on all ring sizes.

RESOLUTE with *BiSS* serial comms is available with the following resolution options:

18 bit (262 144 counts per revolution, \approx 4.94 arc second)

26 bit (67 108 864 counts per revolution, \approx 0.019 arc second)

32 bit (4 294 967 296 counts per revolution, \approx 0.00030 arc second)

Note that 32 bit resolution is below the noise floor of the RESOLUTE encoder.

For resolution options on other protocols, contact your local Renishaw representative.

Speed and accuracy


RESA diameter (mm)	Maximum reading speed (rev/min)	System accuracy (arc second)
52	36 000	\pm 5.49
57	33 000	\pm 4.89
75	25 000	\pm 3.82
100	19 000	\pm 2.86
103	18 500	\pm 2.72
104	18 000	\pm 2.69
115	16 500	\pm 2.44
150	12 000	\pm 1.91
200	9 500	\pm 1.43
206	9 200	\pm 1.42
209	9 000	\pm 1.4
229	8 300	\pm 1.27
255	7 400	\pm 1.11
300	6 300	\pm 0.95
350	5 400	\pm 0.82
413	4 600	\pm 0.69
417	4 500	\pm 0.68
489	3 900	\pm 0.59
550	3 400	\pm 0.52

System accuracy is graduation accuracy plus SDE. Effects such as eccentricity influence installed accuracy; for application advice, contact your local Renishaw representative.

CAUTION: Very high speed motion axes require additional design consideration.
For applications that will exceed 50% of the rated maximum reading speed of the ring, contact your local Renishaw representative.

For REXA speed and accuracy figures, refer to the *REXA* data sheet (Renishaw part no. L-9517-9405).

General specifications (angle and linear)

Power supply	5 V \pm 10%	1.25 W maximum (250 mA @ 5 V)
	Ripple	200 mVpp maximum @ frequency up to 500 kHz maximum
Temperature	Storage	-20 °C to +80 °C
	Operating	0 °C to +80 °C
		For extended temperature range, see the <i>RESOLUTE ETR</i> data sheet (Renishaw part no. L-9517-9420)
Humidity		95% relative humidity (non-condensing) to EN 60068-2-78
Sealing		IP64
Acceleration (readhead)	Operating	500 m/s ² , 3 axes
Shock (readhead)	Non-operating	1000 m/s ² , 6 ms, ½ sine, 3 axes
Maximum acceleration of scale with respect to readhead		BiSS - 2000 m/s ²
		NOTE: This is the worst-case figure that is correct for the slowest communications request rates. For faster request rates, the maximum acceleration of scale with respect to the readhead can be higher. For more details, contact your local Renishaw representative.
Vibration	Operating	300 m/s ² max @ 55 Hz to 2000 Hz, 3 axes
Mass	Readhead	18 g
	Cable	32 g/m
Cable		7 core, tinned and annealed copper, 28 AWG
		Double-shielded, outside diameter 4.7 \pm 0.2 mm
		Flex life > 20 \times 10 ⁶ cycles at 20 mm bend radius
		UL recognised component 
Communication format		RS485/RS422 differential line-driven signal


NOTE: For Vacuum and Extended Temperature Range (ETR) specifications refer to the relevant data sheets.

RESOLUTE installation drawing (on RSLA/RELA scale)

Dimensions and tolerances in mm



For detailed drawings, refer to the RESOLUTE linear or rotary encoder installation guides.



* Extent of mounting faces.


† Thread depth from mounting face. Recommended thread engagement 5 mm (8 including counterbore). Recommended tightening torque 0.5 to 0.7 Nm.

RESOLUTE side exit cable installation drawing (on RSLA/RELA scale)

Dimensions and tolerances in mm



For detailed drawings, refer to the RESOLUTE linear or rotary encoder installation guides.



* Extent of mounting faces.

† Thread depth from mounting face. Recommended thread engagement 5 mm (8 including counterbore). Recommended tightening torque 0.5 to 0.7 Nm.

RESOLUTE angle nomenclature

	RA	26B	AA	052B	30	A
Series						
R = RESOLUTE						
Scale form						
A = Angular						
Protocol						
18B = <i>BiSS</i> 18 bit						
26B = <i>BiSS</i> 26 bit						
32B = <i>BiSS</i> 32 bit						
Mechanical option						
A = Standard IP64						
E = Extended Temperature Range* (standard cable outlet)						
V = Vacuum†						
S = Side cable outlet						
D = Extended Temperature Range* (side cable outlet)						
Gain option						
A = Standard						
Ring diameter						
052 = 52 mm ring						
057 = 57 mm ring						
075 = 75 mm ring						
100 = 100 mm ring						
103 = 103 mm ring						
104 = 104 mm ring						
115 = 115 mm ring						
150 = 150 mm ring						
183 = 183 mm ring (REXA only)						
200 = 200 mm ring						
206 = 206 mm ring						
209 = 209 mm ring						
229 = 229 mm ring						
255 = 255 mm ring						
300 = 300 mm ring						
350 = 350 mm ring						
413 = 413 mm ring (RESA only)						
417 = 417 mm ring						
489 = 489 mm ring (RESA only)						
550 = 550 mm ring (RESA only)						
Scale code option						
B = Standard scale code						
Cable length						
02 = 0.2 m (A and F terminations only)						
05 = 0.5 m						
10 = 1 m						
15 = 1.5 m						
30 = 3 m						
50 = 5 m						
99 = 10 m						
Termination						
A = 9-way D-type connector						
F = flying lead (unterminated)						
V = vacuum flying lead (unterminated)†						

RESOLUTE linear nomenclature


	RL	32B	AS	001C	30	A
Series						
R = RESOLUTE						
Scale form						
L = Linear						
Protocol						
26B = <i>BiSS</i> 26 bit						
32B = <i>BiSS</i> 32 bit						
36B = <i>BiSS</i> 36 bit						
Mechanical option						
A = Standard IP64						
V = Vacuum†						
S = Side cable outlet						
Gain option						
T = RTLA/RTLA-S						
S = RSLA						
E = RELA						
Resolution						
001 = 1 nm						
005 = 5 nm						
050 = 50 nm						
Scale code option						
B = RTLA/RTLA-S (20 mm to 10 m)						
C = RSLA (20 mm to 5 m)/RELA (> 1.13 m to 1.5 m)						
D = RELA (20 mm to 1.13 m)						
E = RTLA/RTLA-S (> 10 m to 21 m)						
Cable length						
02 = 0.2 m (A and F terminations only)						
05 = 0.5 m						
10 = 1 m						
15 = 1.5 m						
30 = 3 m						
50 = 5 m						
99 = 10 m						
Termination						
A = 9-way D-type connector						
F = flying lead (unterminated)						
V = vacuum flying lead (unterminated)†						

* For additional information on the Extended Temperature Range variant, refer to the *RESOLUTE™ ETR* data sheet (Renishaw part no. L-9517-9420).

† For additional information on the Vacuum variant, refer to the *RESOLUTE™ UHV* data sheet (Renishaw part no. L-9517-9530).

NOTE: Not all combinations are valid. Check valid options online at www.renishaw.com/epc

RESOLUTE series compatible products:



For worldwide contact details, visit www.renishaw.com/contact

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

© 2010-2019 Renishaw plc. All rights reserved.

Renishaw reserves the right to change specifications without notice.

RENISHAW and the probe symbol used in the RENISHAW logo are registered trade marks of Renishaw plc in the United Kingdom and other countries.

apply innovation and names and designations of other Renishaw products and technologies are trade marks of Renishaw plc or its subsidiaries.

All other brand names and product names used in this document are trade names, trade marks or registered trade marks of their respective owners.



L - 9517 - 9448 - 04

Part no.: L-9517-9448-04-J
Issued: 09.2019