

RENISHAW, retrofit™ - Step by step guide



Transform your CMM with a Renishaw retrofit

Understanding your requirements

Increased throughput

- 5-axis measurement technology
- · better control of functional fits
- · simpler data analysis, increased consistency
- shorter lead times: faster programming and 'Production mode' operation for faster program execution
- open system allowing your choice of service provider
- · reduced operating costs: lower manning levels, less human error
- freedom: use any I++ DME-compatible metrology software
- future proofed: flexibility to grow with your business





Step 2



Step 1

Quote

Scheduling

Machine survey

The first step in a Renishaw retrofit is a rigorous machine survey designed to assess the condition of mechanical and electrical components of the CMM. Combined with Renishaw's extensive experience with all brands of CMMs, this enables Renishaw to commit to a defined level of system performance. You will know exactly what to expect from your upgraded CMM before you make any commitment.

Utilising the CMM survey results, our quotation document details the specific products and services required in order to achieve the performance capability required by your business, as identified by the previous machine survey and customer requirement identification.

An estimate may have been issued previously for budgetary purposes.

We understand that your CMM's availability is critical and therefore ensure that every item and task required for the retrofit is pre-scheduled in order to minimise the downtime and fit around your production demands.

Step 3









Step 4

Step 5

Step 6

Installation







Calibration

Renishaw is certified by both UKAS (to ISO 17025) and A2LA, giving customers confidence in the accuracy of their upgraded machine, which will be supplied with a UKAS calibration certificate to ISO 10360-2.







Support

We provide maintenance and calibration solutions that can be tailored to match your requirements; as well as functionality to perform regular machine health checks with performance history analysis tools.

Our support website offers immediate access to support and remote diagnostics, the latest UCC and MODUS software downloads, and a knowledgebase that addresses frequently asked questions.

Contract support

To sustain your machine's performance, a range of maintenance contracts are available including services such as annual machine re-calibration and emergency cover. Renishaw's global network allows us to provide you with direct support, wherever you are located.

However, our system is open and the customer owns the system data files, which allows a free choice of service provider for ongoing system maintenance and support.

Renishaw plc

New Mills, Wotton-under-Edge, Gloucestershire, GL12 8JR United Kingdom

+44 (0)1453 524524 +44 (0)1453 524901 uk@renishaw.com

www.renishaw.com

Renishaw retrofit service

A Renishaw retrofit gives users of all brands of CMM access to state-of-the-art technology, with the security of global service and support direct from the manufacturer.

Key features and benefits of our one-stop retrofit service include:

- Unparalleled choice of sensors
- Direct hardware and software support from Renishaw
- Rapid exchange service on all system elements
- UKAS-A2LA accredited calibration
- 5-axis technology



RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

©2011 Renishaw plc. All rights reserved.

Renishaw reserves the right to change specifications without notice

RENISHAW and the probe emblem used in the RENISHAW logo and REVO are registered trademarks of Renishaw plc in the UK and other countries.

apply innovation, Productive Process Pyramid, Productive Process Patterns are trademarks of Renishaw plc.

All other brand names and product names used in this document are trade names, service marks, trademarks or registered trademarks of their respective owners.

Hybrid Part No. H-1000-0061-01-B