


# Air bearing production given a lift


**Customer:**

Air Bearings Ltd

**Industry:**

Precision manufacturing

**Challenge:**

Reduce costs and set-up times, and increase quality when manufacturing batches of multiple precision components.

**Solution:**

Simplified tool setting and workpiece set-up using Renishaw's TS27R tool setter and OMP40 touch-trigger probe.

The rise in the popularity of air bearing spindles for new applications owes much to the ability of modern machine tools to provide extremely tight dimensional tolerances and fine surface finishes. Achieving such results, however, can involve lengthy set-up times; especially where batch production must be combined with frequent tool changes. Air Bearings Ltd (ABL) of Poole, Dorset, a highly successful manufacturer in this expanding field, has tackled this by fitting Renishaw tool setting systems and spindle-mounted touch probes. Not only has this reduced costs, but also sustained ABL's drive for quality improvements.

## Wide range

With a basic product range extending from large, 'slow-speed' spindles and powerful motorised units (1 kW and 80,000 rpm) up to small ultra high-speed (250,000 rpm) spindles, manufacturing flexibility is clearly important. Components to be machined, the majority of which are cylindrical in form, vary in size from as little as 5 mm diameter up to 85 mm diameter and from 3 mm to 235 mm in length. They come in a variety of materials, including aluminium, stainless steel and bronze.

Two of ABL's machine tool suppliers, Fanuc and Haas, independently recommended the use of Renishaw probing

systems as a means of improving productivity. The adoption of the Renishaw probing systems has greatly simplified set-ups in two important respects: tool setting and workpiece checking.

## Cost reduction with quality improvement

John Read, ABL's workshop supervisor, says: "We recently introduced various Renishaw probing systems on a number of our machine tools as part of a cost reduction exercise aimed at reducing set-up times. We found that they could also enable us to introduce multi-load fixtures, instead of using single loading, because they can create and store datum positions on several components. By probing each component on such multi-load fixtures, our policy of continuous quality improvement has been maintained."

## Small as well as large batch production

Renishaw's OMP40 spindle probe and the TS27R tool setting system are installed on each of four of ABL's Fanuc Robodrills. They are also used on a Haas VF1 vertical machining centre, a machine with four-axis capability that handles a high volume



Machined spindles - tight tolerances and good surface finish is paramount

of work with a minimum number of operations. OMP40 probes are also used on two of ABL's Olympic Seiki vertical twin-pallet machines, together with Renishaw TS32S tool setting systems.

The TS27R is a highly flexible, cost effective tool-setting probe for vertical applications. Its compact and robust design allows simple fitting to the machine bed and can be used to set tool lengths in Z and rotating tools in X and Y, for radius offsets. The Renishaw TS32S, with infrared transmission of the probe signal, is used on the Olympic Seiki verticals because these machines utilise twin pallet load/unload systems which would not allow hard-wired systems. The OMP40 spindle-mounted probes have proved to be perfectly suited to the small machines. They are primarily used running on a batch production basis for component referencing and inspection tasks.

### Higher productivity

Founded in 1993, ABL rapidly established itself as a quality supplier of 'competitively priced air bearing spindles that offer a superior performance'. These are sold for use within a variety of specialist applications and the company has won three prestigious Queen's Awards for Enterprise.



Machining centres, equipped with job set-up probes can now run batches of multiple components

### Speeds up to 300,000 rpm

Says ABL's managing director, Mr Kelly Henocq: "Currently, many of our completed spindle assemblies are destined for installation into special-purpose machines designed to drill printed circuit boards. These 'state-of-the-art' production units require the spindles to operate at speeds as high as 300,000 rpm, as well as demanding extremely high dimensional accuracy (with drill run-out to less than 5 microns) throughout the entire speed range".

### Well equipped for the future

ABL is delighted with the dramatic timesaving on job setting that has been achieved, along with the added benefits of increased quality on batches of multiple components. ABL's machining operation puts the company in a more competitive position and it feels well equipped for future developments.

For more information, visit [www.renishaw.com/airbearings](http://www.renishaw.com/airbearings)

**Renishaw plc**  
New Mills, Wotton-under-Edge  
Gloucestershire, GL12 8JR  
United Kingdom

T +44 (0) 1453 524524  
F +44 (0) 1453 524901  
E [uk@renishaw.com](mailto:uk@renishaw.com)  
[www.renishaw.com](http://www.renishaw.com)

For worldwide contact details, visit [www.renishaw.com/contact](http://www.renishaw.com/contact)

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

© 2017 Renishaw plc. All rights reserved.

Renishaw reserves the right to change specifications without notice.

RENISHAW and the probe symbol used in the RENISHAW logo are registered trade marks of Renishaw plc in the United Kingdom and other countries. apply innovation and names and designations of other Renishaw products and technologies are trade marks of Renishaw plc or its subsidiaries. All other brand names and product names used in this document are trade names, trade marks or registered trade marks of their respective owners.



H - 5650 - 3003 - 01

Part no.: H-5650-3003-01-B  
Issued: 02.2017